

ICAN FULL FACE 20-300 Y (20-300 Y, 20-300 YT) is a CE-marked full face mask (class 2) for the protection of the user's eyes and respiratory organs against harmful solid and liquid particles, fumes and gases. The full face mask is tested and approved in accordance with European standards EN 136:1989, prEN 136:1996 (sections 5 and 8) and EN 148-1:1987.

ICAN FULL FACE 20-300 Y is the result of extensive research and development work. Practical trials under extreme working conditions have provided the 20-300 Y with the full face mask's most important properties:

Very high level of protection combined with great comfort for the user when working.

Face blank:

20-300 Y is produced in soft silicone, which does not cause allergic reactions, and gives the user a particularly high degree of hygiene and comfort. The mask's anatomical form provides maximum tightness and comfort. The double seal border along the edge of the mask is an extra safety zone.

Inner mask:

20-300 Y has a soft and non-allergic inner mask in silicone, which in addition to being kind to the skin, reduces misting, improves air exchange and makes the mask more comfortable, even when carrying out physically-exacting tasks. Misting is reduced because the inhalation air is guided up along the inner side of the visor as the inner mask is equipped with two large inhalation valves.

Head harness:

All 20-300 Y's straps can be easily adjusted and quickly released ("quick release"). The straps, which are produced in non-allergic silicone, distribute the weight and pressure on the head and face in an ideal manner, making it comfortable to use the mask for long periods. The construction of the straps allows a safety helmet and ear defenders, for instance, to be used with the mask.

Visor:

20-300 Y is constructed with a large visor which is both resistant to impact and ensures a wide field of vision to all sides. The visor, which has a very high quality optical component, is mounted in a plastic frame.

Exhalation valve:

Exhalation takes place through an exhalation valve which is recessed and well-protected behind a cover in the connection element. This reduces the risk of contamination of the valve. The moist inhaled air is carried directly out of the inner mask, so that the air exchange is improved considerably since the amount of exhaled air remaining in the mask is reduced to a minimum.

Speech membrane:

A built-in speech membrane of synthetic film provides good communication with the surroundings. It is therefore not necessary to leave the polluted area and remove the mask in order to speak to others, and it is also possible to use the telephone without removing the mask.

Inhalation valve:

Inhalation takes place via the inhalation valve, whose natural rubber membrane offers only very low resistance.

Carrying strap:

20-300 Y is supplied with a plastic carrying strap.

Storage brace:

20-300 Y is supplied with a plastic transport and storage brace so that the mask always retains its shape.

TEKNICAL SPECIFICATIONS:

Face blank.....	Silicone
Inner mask.....	Silicone
Buckles.....	"Quick-release" in plastic
Carrying strap.....	Plastic
Head harness.....	Silicone
Visor.....	Perspex/Triplex
Inhalation valve.....	Nature rubber membrane
Exhalation valve.....	Neoprene rubber membrane
Speech membrane.....	Synthetic film
Valve housing.....	Standard thread (EN 148-1:1987)
Weight.....	App. 485 gram
Colour.....	Yellow
Approval.....	EN136:1989 CL.2

ICAN FULL FACE:

Item no.	Description
20-300 Y	ICAN Full Face, perspex visor
20-300 YT	ICAN Full Face, triplex visor
SPARE PARTS:	
Item no.	Description
20-302	Strap set - complete
20-001	Valve set
20-003	Valve housing - complete
20-004	Carrying strap - complete
20-005	Speech membrane set
20-006	Closing band
20-008	Storage brace
20-020	Visor Perspex
20-021	Visor Triplex

Areas of use (examples):

- ★ Chemical production
- ★ Medicine production
- ★ Oil and gas extraction
- ★ Laboratory work
- ★ Painting
- ★ Grain and feedstuff work
- ★ Metal degreasing with solvents
- ★ Spraying with pesticides

Warning!

If the oxygen content of the air is less than 17% (by volume) oxygen, or if the gas concentration exceeds the maximum allowable level for the filter, an air supply must be used which is independent of the surrounding air.

If the polluted air's oxygen content is 17-21% (by volume), ICAN FULL FACE 20-300 Y can be used with a gas, particle or combination filter with standard thread connection. Refer to technical data sheet for ICAN-filters with standard thread connection.

It is important that the full face mask's instruction manual is read carefully before use.